

**Garant**

**Steel boring bar A.. STLCL 90°, for indexable inserts TC.., left-hand, Shank Ø / insert size: 25/16mm**


**Order data**

Order number	260935 25/16
GTIN	4045197653628
Item class	21T

**Technical description**

suitable indexable insert	TC.. 16T3..
Head length $L_1$	41 mm
ISO code toolholder	A25R STFCCR/L16
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Pack of insert screws	269028 8
Insert size	16 mm
Centre offset $L_3$	17 mm
Overall length $L$	200 mm
Clamping height $L_2$	23 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

---

**Accessories**

Set of insert screws Type 8

269028 8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15