

**Garant**

**Steel boring bar A.. STLCL 90°, for indexable inserts TC.., left-hand, Shank Ø / insert size: 32/16mm**


**Order data**

Order number	260935 32/16
GTIN	4045197656070
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	40 mm
Insert size	16 mm
Pack of insert screws	269028 2
Head length $L_1$	34.6 mm
suitable indexable insert	TC.. 16T3..
Shim screw	269013 2
Centre offset $L_3$	22 mm
Shim	269005 7
ISO code toolholder	A32S STFCL/L16
Overall length $L$	250 mm
Clamping height $L_2$	30 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	32 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Shim Type 7	269005 7
Shim screw Type 2	269013 2
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15