

**Garant**

**Steel boring bar A.. STFCR 90°, for indexable inserts TC., right-hand, Shank  
Ø / insert size: 20/16mm**


**Order data**

Order number	260934 20/16
GTIN	4045197653550
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	25 mm
Centre offset $L_3$	13 mm
Pack of insert screws	269028 8
Head length $L_1$	36.6 mm
ISO code toolholder	A20R STFCR/L16
Insert size	16 mm
suitable indexable insert	TC.. 16T3..
Overall length L	200 mm
Clamping height $L_2$	18 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15