

**Garant**

**Steel boring bar A.. STLCL 90°, for indexable inserts TC., left-hand, Shank Ø / insert size: 10/11mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 260935 10/11  |
| GTIN         | 4045197653581 |
| Item class   | 21T           |

**Technical description**

|   |                               |
|---|-------------------------------|
| Insert size                             | 11 mm                         |
| Pack of insert screws                   | 269028 7                      |
| ISO code toolholder                     | A10K STFCCR/L11               |
| Centre offset $L_3$                     | 7 mm                          |
| suitable indexable insert               | TC.. 1102..                   |
| Minimum pre-drill $\varnothing D_{min}$ | 13 mm                         |
| Head length $L_1$                       | 22.8 mm                       |
| Overall length L                        | 125 mm                        |
| Clamping height $L_2$                   | 9 mm                          |
| Setting angle $\kappa$                  | 90 degrees                    |
| Shank $\varnothing D_s$                 | 10 mm                         |
| Standard                                | Works standard                |
| Application type                        | left-hand                     |
| Boring depth up to                      | 3×D                           |
| Through-coolant                         | yes                           |
| Application                             | Internal longitudinal turning |

|                 |            |
|-----------------|------------|
| Type of product | Boring Bar |
|-----------------|------------|

---

## Accessories

|  |            |
|--|------------|
| Set of insert screws Type 7  | 269028 7   |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |