

**Garant**

**Steel boring bar A.. STLCL 90°, for indexable inserts TC.., left-hand, Shank  $\varnothing$  / insert size: 12/11mm**


**Order data**

Order number	260935 12/11
GTIN	4045197653598
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	16 mm
suitable indexable insert	TC.. 1102..
Head length $L_1$	26.5 mm
Centre offset $L_3$	9 mm
Pack of insert screws	269028 7
ISO code toolholder	A12L STFCL/L11
Insert size	11 mm
Overall length $L$	140 mm
Clamping height $L_2$	11 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8