

**Garant**
**Clamping toolholder SVHBR 107,5°, for indexable inserts VB., right-hand,  
Shank / insert size: 16/11mm**

**Order data**

Order number	261106 16/11
GTIN	4045197655479
Item class	21T

**Technical description**

Insert size	11 mm
Functional width L <sub>4</sub>	20 mm
Head length L <sub>1</sub>	13 mm
ISO code toolholder	SVHBR/L 1616H11
suitable indexable insert	VB.. 1103..
Pack of insert screws	269028 22
Shank size	16 mm
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

**Accessories**

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8