

**Garant**

**Clamping toolholder SVVBN 72,5°, for indexable inserts VB., neutral, Shank / insert size: 16/11mm**



## Order data

Order number	261111 16/11
GTIN	4045197655837
Item class	21T

## Technical description

Shank size	16 mm
suitable indexable insert	VB.. 1103..
Overhang L <sub>1</sub> neutral holders	25 mm
Pack of insert screws	269028 22
Overall length L neutral holders	100 mm
Functional width L <sub>4</sub> neutral holders	8 mm
Insert size	11 mm
ISO code toolholder	SVVBN 1616H11
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle $\kappa$	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8