

**Garant**

**Clamping toolholder SVJBR 93°, for indexable inserts VB., right-hand, Shank / insert size: 20/11mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 261108 20/11  |
| GTIN         | 4045197655776 |
| Item class   | 21T           |

## Technical description

|                                 |                               |
|---------------------------------|-------------------------------|
| Shank size                      | 20 mm                         |
| Functional width L <sub>4</sub> | 25 mm                         |
| Insert size                     | 11 mm                         |
| suitable indexable insert       | VB.. 1103..                   |
| Pack of insert screws           | 269028 22                     |
| Head length L <sub>1</sub>      | 23 mm                         |
| ISO code toolholder             | SVJBR/L 2020K11               |
| Overall length L                | 125 mm                        |
| Standard                        | Works standard                |
| Application type                | right-hand                    |
| Through-coolant                 | no                            |
| Setting angle κ                 | 93 degrees                    |
| Application                     | External longitudinal turning |
| Application                     | External longitudinal turning |
| Type of product                 | Boring bar                    |

---

**Accessories**

|                                                                                      |            |
|--------------------------------------------------------------------------------------|------------|
| Set of insert screws Type 22                                                         | 269028 22  |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |