

**Garant****Clamping toolholder SVJBR 93°, for indexable inserts VB., right-hand, Shank / insert size: 20/16mm**

## Order data

Order number	261108 20/16
GTIN	4045197655783
Item class	21T

## Technical description

ISO code toolholder	SVJBR/L 2020K16
Shim screw	269013 2
Shank size	20 mm
suitable indexable insert	VB.. 1604..
Functional width L <sub>4</sub>	25 mm
Head length L <sub>1</sub>	30 mm
Pack of insert screws	269028 2
Insert size	16 mm
Shim	269005 8
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8