

Garant

Clamping toolholder SVVBN 72,5°, for indexable inserts VB., neutral, Shank / insert size: 25/11mm



Order data

Order number	261111 25/11
GTIN	4045197655851
Item class	21T

Technical description

Overall length L neutral holders	150 mm
Overhang L ₁ neutral holders	39 mm
Insert size	11 mm
suitable indexable insert	VB.. 1103..
ISO code toolholder	SVVBN 2525M11
Functional width L ₄ neutral holders	12.5 mm
Pack of insert screws	269028 22
Shank size	25 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8