

Garant**Clamping toolholder SVJBR 93°, for indexable inserts VB., right-hand, Shank / insert size: 25/16mm**

Order data

Order number	261108 25/16
GTIN	4045197653635
Item class	21T

Technical description

Shank size	25 mm
Shim	269005 8
Pack of insert screws	269028 2
Shim screw	269013 2
Head length L ₁	33 mm
ISO code toolholder	SVJBR/L 2525M16
suitable indexable insert	VB.. 1604..
Functional width L ₄	32 mm
Insert size	16 mm
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8