

Garant
**Clamping toolholder SVHBR 107,5°, for indexable inserts VB., right-hand,
Shank / insert size: 25/16mm**

Order data

Order number	261106 25/16
GTIN	4045197655707
Item class	21T

Technical description

Shim screw	269013 2
Functional width L ₄	32 mm
Pack of insert screws	269028 2
ISO code toolholder	SVHBR/L 2525M16
Shank size	25 mm
suitable indexable insert	VB.. 1604..
Head length L ₁	21 mm
Shim	269005 8
Insert size	16 mm
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8