

Garant

Clamping toolholder SVVBN 72,5°, for indexable inserts VB., neutral, Shank / insert size: 20/16mm



Order data

Order number	261111 20/16
GTIN	4045197655868
Item class	21T

Technical description

Shim screw	269013 2
Insert size	16 mm
suitable indexable insert	VB.. 1604..
Overall length L neutral holders	125 mm
Overhang L ₁ neutral holders	31 mm
ISO code toolholder	SVVBN 2020K16
Pack of insert screws	269028 2
Functional width L ₄ neutral holders	10 mm
Shim	269005 8
Shank size	20 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8