

Garant

**Clamping toolholder SVHBL 107,5°, for indexable inserts VB., left-hand,
Shank / insert size: 12/11 mm**



Order data

Order number	261107 12/11
GTIN	4045197655714
Item class	21T

Technical description

Insert size	11 mm
Shank size	12 mm
Pack of insert screws	269028 22
ISO code toolholder	SVHBR/L 1212F11
Functional width L_4	16 mm
Head length L_1	13 mm
suitable indexable insert	VB.. 1103..
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8