

**Garant**

**Clamping toolholder SVVBN 72,5°, for indexable inserts VB., neutral, Shank / insert size: 25/16mm**



## Order data

Order number	261111 25/16
GTIN	4045197655875
Item class	21T

## Technical description

Functional width L <sub>4</sub> neutral holders	12.5 mm
Shim screw	269013 2
Overhang L <sub>1</sub> neutral holders	39 mm
Pack of insert screws	269028 2
ISO code toolholder	SVVBN 2525M16
Insert size	16 mm
Shim	269005 8
suitable indexable insert	VB.. 1604..
Overall length L neutral holders	150 mm
Shank size	25 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8