

Garant

Clamping toolholder SVJBL 93°, for indexable inserts VB., left-hand, Shank / insert size: 20/11mm



Order data

Order number	261109 20/11
GTIN	4045197655806
Item class	21T

Technical description

suitable indexable insert	VB.. 1103..
ISO code toolholder	SVJBR/L 2020K11
Insert size	11 mm
Shank size	20 mm
Functional width L ₄	25 mm
Head length L ₁	23 mm
Pack of insert screws	269028 22
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8