

Garant

Clamping toolholder SVJBL 93°, for indexable inserts VB., left-hand, Shank / insert size: 20/16mm



Order data

Order number	261109 20/16
GTIN	4045197655813
Item class	21T

Technical description

Insert size	16 mm
Shank size	20 mm
Functional width L_4	25 mm
Head length L_1	30 mm
suitable indexable insert	VB.. 1604..
Shim screw	269013 2
Pack of insert screws	269028 2
Shim	269005 8
ISO code toolholder	SVJBR/L 2020K16
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8