

Garant

**Clamping toolholder SVHBL 107,5°, for indexable inserts VB., left-hand,
Shank / insert size: 20/16mm**



Order data

Order number	261107 20/16
GTIN	4045197655745
Item class	21T

Technical description

ISO code toolholder	SVHBR/L 2020K16
Shim	269005 8
Shim screw	269013 2
Pack of insert screws	269028 2
Head length L ₁	16 mm
Insert size	16 mm
Functional width L ₄	25 mm
Shank size	20 mm
suitable indexable insert	VB.. 1604..
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8