

**Garant**

**Clamping toolholder SVHBR 107,5°, for indexable inserts VB., right-hand,  
Shank / insert size: 12/11 mm**


**Order data**

Order number	261106 12/11
GTIN	4045197655462
Item class	21T

**Technical description**

Shank size	12 mm
suitable indexable insert	VB.. 1103..
ISO code toolholder	SVHBR/L 1212F11
Functional width L <sub>4</sub>	16 mm
Head length L <sub>1</sub>	13 mm
Insert size	11 mm
Pack of insert screws	269028 22
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8