

Garant

**Steel boring bar A.. SVQBR 107,5°, for indexable inserts VB., right-hand,
Shank Ø / insert size: 25/16mm**


Order data

Order number	261130 25/16
GTIN	4045197653659
Item class	21T

Technical description

Pack of insert screws	269028 8
Insert size	16 mm
Centre offset L_3	17 mm
ISO code toolholder	A25R SVQBR/L16
Head length L_1	40 mm
Minimum pre-drill $\varnothing D_{min}$	32 mm
suitable indexable insert	VB.. 1604..
Overall length L	200 mm
Clamping height L_2	23 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15