

Garant**Side lock arbor Form ADB, SK 40 A = 200, Clamping range Ø D1: 25mm**

Order data

Order number	300285 25
GTIN	4045197283269
Item class	31A

Description

Version:

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping Ø D ₁	25 mm
Overhang dimension A	200 mm
Spare clamping screw No. 30 9900	25
External Ø D	65 mm
Adapter	SK 40 A = 200
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm

Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull studsealed suitable for steep tapers 40	308635 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studForm B suitable for steep tapers 40	308640 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Spare clamping screw for chucks with clamping Ø D1 25 mm	309900 25