

**Garant**
**Clamping toolholder SVHCL 107,5°, for indexable inserts VC., left-hand,  
Shank / insert size: 25/16mm**

**Order data**

Order number	261309 25/16
GTIN	4045197653802
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	32 mm
Head length L <sub>1</sub>	23.5 mm
suitable indexable insert	VC.. 1604..
Shim	269005 8
Pack of insert screws	269028 2
Insert size	16 mm
Shim screw	269013 2
ISO code toolholder	SVHCR/L 2525M16
Shank size	25 mm
Overall length L	150 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15