

Garant

**Clamping toolholder SVHCR 107,5°, for indexable inserts VC., right-hand,
Shank / insert size: 12/11mm**



Order data

Order number	261308 12/11
GTIN	4045197655882
Item class	21T

Technical description

Shank size	12 mm
Head length L ₁	13 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVHCR/L 1212F11
Pack of insert screws	269028 22
Functional width L ₄	16 mm
Insert size	11 mm
Overall length L	80 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8