

Garant
Clamping toolholder SVJCR 93°, for indexable inserts VC., right-hand, Shank / insert size: 12/11mm

Order data

Order number	261312 12/11
GTIN	4045197655943
Item class	21T

Technical description

Shank size	12 mm
Pack of insert screws	269028 22
Functional width L ₄	16 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVJCR/L 1212F11
Head length L ₁	21.5 mm
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8