

Garant
Clamping toolholder SVJCL 93°, for indexable inserts VC., left-hand, Shank / insert size: 20/16mm

Order data

Order number	261313 20/16
GTIN	4045197653888
Item class	21T

Technical description

Shim screw	269013 2
ISO code toolholder	SVJCR/L 2020K16
Shank size	20 mm
Functional width L ₄	25 mm
suitable indexable insert	VC.. 1604..
Insert size	16 mm
Pack of insert screws	269028 2
Head length L ₁	29.5 mm
Shim	269005 8
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15