

**Garant**

**Clamping toolholder SVHCR 107,5°, for indexable inserts VC., right-hand,  
Shank / insert size: 16/11mm**



### Order data

Order number	261308 16/11
GTIN	4045197655899
Item class	21T

### Technical description

Shank size	16 mm
Pack of insert screws	269028 22
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVHCR/L 1616H11
Functional width L <sub>4</sub>	20 mm
Insert size	11 mm
Head length L <sub>1</sub>	13 mm
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8