

**Garant**
**Clamping toolholder SVHCR 107,5°, for indexable inserts VC., right-hand,  
Shank / insert size: 20/16mm**

**Order data**

Order number	261308 20/16
GTIN	4045197653772
Item class	21T

**Technical description**

Head length L <sub>1</sub>	15 mm
ISO code toolholder	SVHCR/L 2020K16
Insert size	16 mm
suitable indexable insert	VC.. 1604..
Shank size	20 mm
Pack of insert screws	269028 2
Shim screw	269013 2
Shim	269005 8
Functional width L <sub>4</sub>	25 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15