

**Garant**

**Clamping toolholder SVJCR 93°, for indexable inserts VC., right-hand, Shank / insert size: 20/16mm**



## Order data

Order number	261312 20/16
GTIN	4045197653840
Item class	21T

## Technical description

Shim screw	269013 2
Pack of insert screws	269028 2
Shim	269005 8
Insert size	16 mm
Head length L <sub>1</sub>	29.5 mm
Functional width L <sub>4</sub>	25 mm
ISO code toolholder	SVJCR/L 2020K16
Shank size	20 mm
suitable indexable insert	VC.. 1604..
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15