

Garant
**Clamping toolholder SVHCL 107,5°, for indexable inserts VC., left-hand,
Shank / insert size: 12/11 mm**

Order data

Order number	261309 12/11
GTIN	4045197655912
Item class	21T

Technical description

Shank size	12 mm
Insert size	11 mm
Pack of insert screws	269028 22
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVHCR/L 1212F11
Functional width L ₄	16 mm
Head length L ₁	13 mm
Overall length L	80 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8