

Garant

Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 25/16mm



Order data

Order number	261317 25/16
GTIN	4045197653949
Item class	21T

Technical description

Shim screw	269013 2
Functional width L ₄ neutral holders	12.5 mm
Overall length L neutral holders	150 mm
ISO code toolholder	SVVCN 2525M16
suitable indexable insert	VC.. 1604..
Overhang L ₁ neutral holders	38 mm
Insert size	16 mm
Shank size	25 mm
Pack of insert screws	269028 2
Shim	269005 8
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15