

**Garant**

**HSS boring bar AH.. SVUCR 93°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 20/11mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 261334 20/11  |
| GTIN         | 4045197654021 |
| Item class   | 21T           |

## Technical description

|                                      |                 |
|--------------------------------------|-----------------|
| Insert size                          | 11 mm           |
| ISO code toolholder                  | AH20R SVUCR/L11 |
| Head length L <sub>1</sub>           | 24 mm           |
| Pack of insert screws                | 269028 7        |
| Minimum pre-drill Ø D <sub>min</sub> | 25 mm           |
| suitable indexable insert            | VC.. 1103..     |
| Centre offset L <sub>3</sub>         | 13 mm           |
| Overall length L                     | 200 mm          |
| Clamping height L <sub>2</sub>       | 18 mm           |
| Setting angle κ                      | 93 degrees      |
| Shank Ø D <sub>s</sub>               | 20 mm           |
| Standard                             | Works standard  |
| Application type                     | right-hand      |
| Boring depth up to                   | 5×D             |
| Tool material                        | HSS             |
| Through-coolant                      | yes             |

|                 |                               |
|-----------------|-------------------------------|
| Application     | Internal longitudinal turning |
| Type of product | Boring Bar                    |

---

## Accessories

|                                                                                      |            |
|--------------------------------------------------------------------------------------|------------|
| Set of insert screws Type 7                                                          | 269028 7   |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |