

Garant

HSS boring bar AH.. SVUCL 93°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	261335 16/11
GTIN	4045197654045
Item class	21T

Technical description

Centre offset L_3	11 mm
Minimum pre-drill $\varnothing D_{\min}$	21 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Head length L_1	20 mm
Pack of insert screws	269028 7
ISO code toolholder	AH16Q SVUCR/L11
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8