

Garant

Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 16/11mm



Order data

Order number	261317 16/11
GTIN	4045197653901
Item class	21T

Technical description

Pack of insert screws	269028 22
suitable indexable insert	VC.. 1103..
Functional width L ₄ neutral holders	8 mm
Insert size	11 mm
ISO code toolholder	SVVCN 1616H11
Overhang L ₁ neutral holders	25 mm
Shank size	16 mm
Overall length L neutral holders	100 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8