

**Garant**

**Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 20/11mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 261317 20/11  |
| GTIN         | 4045197653918 |
| Item class   | 21T           |

## Technical description

|   |                               |
|---|-------------------------------|
| Overhang L <sub>1</sub> neutral holders         | 31 mm                         |
| Insert size                                     | 11 mm                         |
| ISO code toolholder                             | SVVCN 2020K11                 |
| Pack of insert screws                           | 269028 22                     |
| suitable indexable insert                       | VC.. 1103..                   |
| Functional width L <sub>4</sub> neutral holders | 10 mm                         |
| Overall length L neutral holders                | 125 mm                        |
| Shank size                                      | 20 mm                         |
| Standard  | Works standard                |
| Application type                                | neutral                       |
| Through-coolant                                 | no                            |
| Setting angle κ                                 | 72.5 degrees                  |
| Application                                     | External longitudinal turning |
| Application                                     | External longitudinal turning |
| Application                                     | External longitudinal turning |

|                 |            |
|-----------------|------------|
| Type of product | Boring bar |
|-----------------|------------|

---

## Accessories

|  |            |
|--|------------|
| Set of insert screws Type 22   | 269028 22  |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |