

Garant

Steel boring bar A.. SVJCR 142°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	261338 16/11
GTIN	4045197654076
Item class	21T

Technical description

Head length L_1	30 mm
ISO code toolholder	A16M SVJCR/L11
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 7
Insert size	11 mm
Centre offset L_3	2 mm
Neck width L_4	9.5 mm
Minimum pre-drill $\varnothing D_{min}$	22 mm
Overall length L	150 mm
Clamping height L_2	15 mm
Setting angle κ	142 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8