

**Garant**

**Steel boring bar A.. SVQCL 107,5°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 40/16mm**


**Order data**

Order number	261345 40/16
GTIN	4045197656209
Item class	21T

**Technical description**

Shim screw	269013 2
Shim	269005 8
Pack of insert screws	269028 2
Insert size	16 mm
Head length L <sub>1</sub>	40 mm
suitable indexable insert	VC.. 1604..
Minimum pre-drill Ø D <sub>min</sub>	49 mm
ISO code toolholder	A40T SVQCR/L16
Centre offset L <sub>3</sub>	27 mm
Overall length L	300 mm
Clamping height L <sub>2</sub>	39 mm
Setting angle κ	107.5 degrees
Shank Ø D <sub>s</sub>	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15