



## Reducing adapter, Shank $\varnothing$ d1 / clamping $\varnothing$ d2: 40/25mm



### Order data

Order number	319426 40/25
GTIN	4045197586834
Item class	32V

### Description

#### Version:

Suitable for VDI arbors form E2 (No. 319275 – 319405).

Suitable for internal cooling, not slotted. Tool is fixed and clamped with 2 clamping screws.

#### Application:

For  $\varnothing$  reduction for tools with plain shanks.

### Technical description

Version	Slot
Shank $\varnothing$ D <sub>1</sub>	40 mm
$\varnothing$ d <sub>4</sub>	44 mm
l <sub>1</sub>	58 mm
l <sub>2</sub>	5 mm
Clamping range $\varnothing$ d <sub>2</sub>	25 mm
Type of product	Reducing adapter

