

**Reducing adapter, Shank  $\varnothing$  d1 / clamping  $\varnothing$  d2: 25/14mm****Order data**

Order number	319426 25/14
GTIN	4045197586612
Item class	32V

**Description****Version:**

Suitable for VDI arbors form E2 (No. 319275 – 319405).

Suitable for internal cooling, not slotted. Tool is fixed and clamped with 2 clamping screws.

**Application:**

For  $\varnothing$  reduction for tools with plain shanks.

**Technical description**

Version	Slot
$\varnothing$ d <sub>4</sub>	29 mm
l <sub>1</sub>	50 mm
Shank $\varnothing$ D <sub>1</sub>	25 mm
Clamping range $\varnothing$ d <sub>2</sub>	14 mm
l <sub>2</sub>	4 mm
Type of product	Reducing adapter