

**Reducing adapter, Shank  $\varnothing$  d1 / clamping  $\varnothing$  d2: 32/20mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 319426 32/20  |
| GTIN         | 4045197586735 |
| Item class   | 32V           |

**Description****Version:**

Suitable for VDI arbors form E2 (No. 319275 – 319405).

Suitable for internal cooling, not slotted. Tool is fixed and clamped with 2 clamping screws.

**Application:**

For  $\varnothing$  reduction for tools with plain shanks.

**Technical description**

|   |                  |
|---|------------------|
| Version                                     | Slot             |
| $l_1$                                       | 58 mm            |
| Clamping range $\varnothing$ d <sub>2</sub> | 20 mm            |
| $l_2$                                       | 5 mm             |
| Shank $\varnothing$ D <sub>1</sub>          | 32 mm            |
| $\varnothing$ d <sub>4</sub>                | 40 mm            |
| Type of product                             | Reducing adapter |

