



Heavy-duty chuck, BT 40, Ø D1: 20mm



Order data

Order number	302865 20
GTIN	4045197549075
Item class	32A

Description

Version:

- **Low friction due to needle bearings.**
- **Protected with anti-corrosion coating.**
- **Dust-tight and watertight.**
- **Very high clamping force prolongs tool life and improves surface quality.**
- **Flexible clamping range by means of collets.**
- **Clamping force up to 1000 Nm.**

Callout:

Internal axial recesses effectively prevent the tool slipping.

High radial stiffness due to repeatable clamping accuracy against a flat face, which prevents misalignment and ensures a high accuracy of machining, coupled with long tool life.

T-slots take up the oil and grease, so that reliable torque transmission is achieved.

Absolutely smooth running of the clamping nut.

Application:

For clamping tools with plain shanks.

Supplied with:

Clamping nut

Optional extras:

C wrench No. 628400.

Pull studs No. 308760 – 308795.

Collets No. 309566 – 309570.

Technical description

Collet outer Ø D	52 mm
------------------	-------

Overhang dimension A	90 mm
Suitable C-hook (pin) spanner No. 628400	52 / 55
Clamping $\varnothing D_1$	20 mm
Adapter	BT 40
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Heavy-duty chuck

Accessories

Collet for heavy-duty chuck Nominal clamping $\varnothing d$ 10 mm	309575 10
Collet for heavy-duty chuck Nominal clamping $\varnothing d$ 8 mm	309575 8
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Collet for heavy-duty chuck Nominal clamping $\varnothing d$ 6 mm	309575 6
Collet for heavy-duty chuck Nominal clamping $\varnothing d$ 16 mm	309575 16
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Collet for heavy-duty chuck Nominal clamping $\varnothing d$ 12 mm	309575 12
C-hook (pin) spannerwith square pin for external nut \varnothing 52/55 mm	628400 52/55
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Collet for heavy-duty chuck Nominal clamping $\varnothing d$ 14 mm	309575 14