

Garant**Short drill chuck Form ADB, BT 50, Clamping range: 0,5-16mm****Order data**

Order number	303176 0,5-16
GTIN	4045197584397
Item class	31B

Description**Version:**

For clockwise and anticlockwise rotation.

Concentricity $\leq 20 \mu\text{m}$.

With through coolant feed up to max. 50 bar.

Supplied with:

Clamping wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	110 mm
Spare chuck key No. 627425	6 AF
Clamping range	0.5 - 16 mm
External $\varnothing$ D	57 mm
Adapter	BT 50
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	ADB
Through-coolant	yes, with max. 50 bar

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 µm
Type of product	Short drill chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50