

Garant
Side lock arbor, HSK-A 63 short, Clamping range \varnothing D1: 25mm

Order data

Order number	304270 25
GTIN	4045197288462
Item class	31A

Description
Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth cutting action!).

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Overhang dimension A	110 mm
Spare clamping screw No. 30 9900	25
Clamping \varnothing D ₁	25 mm
External \varnothing D	65 mm
Adapter	HSK-A 63 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Socket wrench for coolant tubes for HSK 25	309890 25
HSK coolant tube for HSK 25	309880 25
Spare clamping screw for chucks with clamping \varnothing D1 25 mm	309900 25