

Garant**Face mill arbor, HSK-A 100 A = 160, Spigot Ø d1: 40mm****Order data**

Order number	306690 40
GTIN	4045197290502
Item class	31A

Description**Version:**

- Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.
- With Balluff/RFID chip bore.
- Increased collar contact surface.
- HSK mating faces machined.

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

Overhang dimension A	160 mm
Milling mandrel length L ₄	27 mm
Spare milling cutter lock screw No. 309860 / 309861	40
Suitable toggle spanner No. 309840	40
Spigot Ø d ₁	40 mm

External Ø D	89 mm
Clamping Ø D ₁	40 mm
Adapter	HSK-A 100 A = 160
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 40 mm	309840 40
Milling cutter lock screw for mandrel Ø 40 mm	309860 40
HSK coolant tube for HSK 40	309880 40
Socket wrench for coolant tubes for HSK 40	309890 40
Bolt for T-nuts for spigot Ø D1 40 mm	309896 40
Half-round T-nut for face mill arbors For size 40	309898 40