



## Workshop vernier caliper with mm and inch graduations, Measuring range: 750mm



### Order data

Order number	415100 750
GTIN	4045197203175
Item class	41Z

### Description

#### Version:

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

### Technical description

Locking	Locking screw at top
Reversible reading	mm / inch
Jaw length	150 mm
Measuring range	0 - 750 mm
Calibration	A1
Internal jaw $\varnothing$	20 mm
Type of measurement face	hardened
Graduation	1/128 in
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385

Measurement deviation E MPE	± 0.12 mm
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Workshop calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000