

Garant**Square frame level with adjustable vial, Base Length×Accuracy: 150/2mm****Order data**

Order number	469190 150/2
GTIN	4045197519245
Item class	41H

Description**Version:**

Sturdy frame of high quality special casting; hammer finish. 3 sides Vee ground, 1 side flat. One longitudinal and one transverse vial each of glass. The sensitivity (scale value) of the longitudinal vial is specified on the square. Accuracy grade 1 has insulated handles on the housing and protective glass cover over the vials.

Adjustment of the longitudinal vial:

An adjustment screw allows the longitudinal vial to be reset to the 0 position easily and without play, with no need for disassembly.

Application:

For aligning horizontal and vertical faces, shafts etc. and for accurate alignment at a 90° angle.

Standard:**DIN 877****Accuracy:**

1 = with very high sensitivity longitudinal vial **0.02 mm/m.**

2 = with high sensitivity longitudinal vial **0.1 mm/m.**

Note:

Magnetic version available on request.

Technical description

Sole length	150 mm
Sole width	40 mm
Scale divisions	0.1 mm/m
Accuracy class	2
Standard	DIN 877
Packaging	sturdy box
Calibration	H1
Type of product	Spirit level

Services

CalibrationSquare frame level Accuracy 0,10 mm/m	026600 0,10
--	-------------