



## Digital caliper for left-hand use, Measuring range: 150mm



### Order data

Order number	412812 150
GTIN	4045197422828
Item class	42A

### Description

#### Version:

Large, sharp-contrast digital display. The measuring faces are precision-lapped.  
With plastic housing, **for left-handed use.**

#### Supplied with:

Battery No. 081560 size LR44.

### Technical description

Material of the housing	Plastic
Standard	ISO 13385
Jaw length	40 mm
Reversible reading	mm / inch
suitable for left-handed use	yes
Calibration	A1
Depth gauge	rectangular 3.7×1.3
Depth gauge available	yes
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Number of batteries contained	1

Article no of the battery / rechargeable battery fitted	081560 LR44
Power supply	Battery-powered
Measurement deviation E MPE	$\pm 0.03$ mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

### Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

### Accessories

Button cell / special battery Battery type LR44	081560 LR44
---	-------------