



## Vernier caliper with extra long jaws, Measuring range: 1000mm



### Order data

Order number	415188 1000
GTIN	4045197479877
Item class	41Z

### Description

#### Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component Ø.** With fine adjustment. Offset and rounded jaw ends for internal measurements.

With **extra long jaws**, without fine adjustment.

### Technical description

Scale divisions	0.05 mm
Type of caliper jaws	extra long measuring jaws
Internal jaw Ø	20 mm
Jaw length	300 mm
Calibration	A1
Type of measurement face	hardened
Type of reading parts	satin chrome-plated
Weight	3.9 kg
Measuring range	0 - 1000 mm

Graduation	1/20 mm
Error limit	0.2 mm
Packaging	sturdy box
Standard	Manufacturer's standard
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

### Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000
CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000