



Digital dial indicator 0.01 mm reading, Measuring range: 12,5mm



Order data

Order number	434004 12,5
GTIN	4045197435330
Item class	42C

Description

Version:

Digital dial indicator in compact design with high-contrast digital display.

- **Reversible direction of measurement.**
- **Very narrow casing.**

Version of the advertising text:

Digital dial indicator in compact design with high-contrast digital display.

Supplied with:

Supplied with an eye on the cover and 1 battery No. 081560 size CR2032.

Optional extras:

Spare and special contact points No. 434900; 434910; 434915.

Technical description

Gauging force	0.8 – 1.4 N
Calibration	C1
Measuring range	12.5 mm
Thickness of housing	26 mm

Body Ø	58 mm
Reversible reading	0.0005 in
Reversible reading	0.01 mm
Clamping shank - Ø h7	8 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement variation E MPE (measurement range)	0.025 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Packaging	sturdy box
Type of product	dial gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023000 12,5
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

Accessories

Steel contact point Type 11/30	434900 11/30
Steel contact point Type 11/15	434900 11/15
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 29/20	434900 29/20
Carbide contact point Type 2	434910 2
Steel contact point Type 20	434900 20
Steel contact point Type 18/5	434900 18/5
Angled bracket for dial indicator60° Clamping length 50 mm	434918 50

Button cell / special battery Battery type CR2032	081560 CR2032
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 11/35	434900 11/35
Carbide contact point Type 14	434910 14
Carbide contact point Type 18/3	434910 18/3
Steel contact point Type 12	434900 12
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 2	434900 2
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 18/3	434900 18/3
Extension for contact points Length L 50 mm	434920 50
Carbide contact point Type 11	434910 11
Steel contact point Type 15	434900 15
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 18/4	434900 18/4
Steel contact point Type 39	434900 39
Angled bracket for dial indicator45° Clamping length 25 mm	434917 25
Extension for contact points Length L 80 mm	434920 80
Steel contact point Type 17	434900 17
Extension for contact points Length L 10 mm	434920 10
Angled bracket for dial indicator45° Clamping length 50 mm	434917 50
Carbide contact point Type 18/1	434910 18/1
Carbide contact point Type 16	434910 16
Ruby contact point Type 2	434915 2
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 14/20	434900 14/20
Angled bracket for dial indicator60° Clamping length 25 mm	434918 25

Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 24	434900 24
Carbide contact point Type 10	434910 10
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 11	434900 11
Pivoting contact point	434912
Extension for contact points Length L 20 mm	434920 20
Extension for contact points Length L 15 mm	434920 15
Steel contact point Type 28	434900 28
Carbide contact point Type 17	434910 17
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 18/6	434900 18/6
Steel contact point Type 14	434900 14
Extension for contact points Length L 70 mm	434920 70
Extension for contact points Length L 100 mm	434920 100
Steel contact point Type 13	434900 13
Extension for contact points Length L 90 mm	434920 90
Steel contact point Type 14/15	434900 14/15
Steel contact point Type 16	434900 16
Steel contact point Type 11/20	434900 11/20
Carbide contact point Type 18/2	434910 18/2
Extension for contact points Length L 30 mm	434920 30
Extension for contact points Length L 60 mm	434920 60
Steel contact point Type 10	434900 10
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 29/10	434900 29/10