

**External quick caliper with dial gauge, Measuring range: 0-10mm****Order data**

Order number	438545 0-10
GTIN	4045197634641
Item class	42C

Description**Version:**

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Application:

For quick measuring of external grooves, wall thicknesses, plates, pipe wall thicknesses, foils etc.

Technical description

Carbide spherical point Ø	2 mm
Scale divisions	0.1 mm
Measuring range	0 - 10 mm
Dial indicator Ø	50 mm
maximum contact point length L (measurement depth)	36 mm
Error limit	0.1 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Calibration	C7
Type of product	External quick callipers

Services

Calibration	External / internal quick caliper Type S	023450 S
DAkkS calibration	External / internal quick caliper Type S	023460 S