



Vernier depth gauge, Measuring range: 100mm



Order data

Order number	418000 100
GTIN	4045197326997
Item class	41Z

Description

Version:

Measuring beam and vernier with clearly engraved scales. Precision ground contact faces. Vernier satin chrome-plated. Measuring beam equipped with a hardened, fine gauging pin at the front (1.0 mm \varnothing , 8 mm long). **Reversible beam.**

Supplied with:

From size 500 in a case.

Technical description

Vernier length	39 mm
Measuring range	0 - 100 mm
Measuring tip a	1 mm
Bridge length	50 mm
Cross-section measuring beam	8×3 mm
Measuring tip b	8 mm
Graduation	1/20 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Calibration	A1
Type of product	Depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200